

WHITE SHARK

User Manual

TAUS

FOODSERVICEEQUIPMENT

Stream line

WARRANTY CARD / JAMSTVENI LIST

RECEIPT NO. / DATE OF PURCHASE: [Blank] / [Blank]

SELLER'S (POINT COMPANY): [Blank]

THE CUSTOMER: [Blank]

WARRANTY PERIOD (MONTHS): **24**

SIGNATURE / STAMP: [Blank]

DATE: [Blank]

Model No: DSM-03 TAUS

CONTENTS

English 01-06


Croatian 07-12

Deutsch 13-18

Specification

Microphone-core	Dia.14mm Condenser
Polar Pattern	Cardioid
Frequency Response	20Hz-20kHz
Sensitivity	-13.5dBFS -0.5dBFS (±3dB, 94dB SPL at 1kHz)
Maximum SPL	93.5dB
S/N Ratio	60dB
Cable	USB A to B cable

Introduction



USB Microphone

Mic gain control knob

Microphone installation ring

Foam Windscreen


Tripod

USB Cable


Items in package

USB Microphone	x1	Tripod	x1
USB Cable	x1	Foam Windscreen	x1
Microphone installation ring	x1	User Manual	x1


Installation quick guide



Microphone placement




Connect to Computer




How to setting on computer


Windows 10,8,7



Setting microphone level



How to setting on Apple Mac



Model No: DSM-03 TAUS


Technical support:
info@whiteshark.gg
www.whiteshark.gg

Made in China

Karakteristike

Jažrga mikrofona:	Promjer: 14 mm kondenzatorski
Umjenosnost:	Kardioid
Frekvencijski opseg:	20 Hz - 20 kHz
Otpjetnost:	-13.5 dBFS -0.5 dB FS (±3 dB, 94 dB SPL pri 1 kHz)
Maksimalna SPL:	93.5 dB
Odnos signala/šum:	60 dB
Kabel:	USB A -> B kabel

Uvod i opis proizvoda



USB mikroskop

Kolotič za pojačavanje mikrofona

Zglob za montiranje na stalak

Spuzvica za mikroskop


Tronožac

USB kabel


Sadržaj pakiranja

USB mikroskop	x1	Tronožac	x1
USB A - B Kabel	x1	Spuzvica za mikroskop	x1
Zglob za montiranje na stalak	x1	Upute	x1


Kratka uputstva



Postavljanje mikrofona (orijentacija)




Spajanje s računalom




Podešavanje na računalu


Windows 10,8,7



Podešavanje osjetljivosti/glasnoće mikrofona




Kako USB mikroskop koristiti na Apple Mac



Spezifikation

Mikrofonkern-kern	Dia.14mm Condensator
Polar-Muster	Nierencharakteristik
Frequenzgang	20Hz-20kHz
Sensitivität	-13.5dBFS -0.5dBFS (±3dB, 94dB SPL bei 1kHz)
Max. SPL	93.5dB
S/N Verhältnis	60dB
Kabel	USB A bis B cable

Einführung



USB Mikroskop

Mikrofonverstärkung anlage

Installationsring

Tischständer


USB Kabel

Schaumstoffschleibe


Paketinhalt

USB Mikroskop	x1	Tischständer	x1
Installationsänderung	x1	Schaumstoffschleibe	x1
Gebrauchsanweisung	x1	USB Kabel	x1


Installations-Kurzanleitung



Mikrofonplatzierung




Verbinden mit Ihrem Computer




Wie nehmen Sie Einstellungen auf Ihrem Windows vor?

Windows 10,8,7



Einstellung der mikroebene



Wie nehmen Sie Einstellungen auf Ihrem Apple Mac vor?

